GET TO KNOW OUR TRUE FLOW VALVE K, Y, & 3-Way True Flow valve options

FLIPPER

Standard 50° slope, Flipper and Discharge Leg prevents product from slowing through the True Flow valve

Œ 0 6

62

000

2

ඛ

3

OPTIONAL INTERNAL LINING

Without changing the True Flow valve body, the internal Lining can be upgraded between multiple materials.

Urethane • AR Plate • Ceramic Tile

 \mathbf{a}

3

ð

ි

3

5

3

100

ad

FLIPPER DOOR

The Flipper Door allows easy access to the flipper for maintenance without removing the True Flow valve from service.

I D F

Holly Products. 0 We Make it Happen. 2501 Murray St. Suite A • Sioux City, IA 51111 • www.idfi.com

SHAFT SEAL The Lower Shaft Seal prevents product contamination

6

0

2

INFO.

IDFI's Holly True Flow System provides a worry-free design that has been proven since the late 1980's. An internal rod seal assures product separation. The side access panel allows the inline removal & replacement of the flipper to reduce down time.

(C)

Ø

(0)

ACCESS COVER

Easy to remove cover, making maintenance and access to the Internal Lining a breeze.

DRIVE OPTIONS

The Torque Pin Mount allows multiple drive options. **AIR • ELECTRIC • MANUAL • HYDRAULIC**

DISCHARGE LEG FLANGE

The 45° Standard outlet with optional wedge, to change the discharge leg degree.



0